

Row Marker Tubes

For use with Glaser Adjustable Rakes Nos. 100 and 123



These Row Marker Tubes are not made by Glaser GMBH in Switzerland but produced by us from hard white plastic tube sourced in the UK.

Eliot Coleman had the idea of fitting hard plastic tubes to the Glaser rakes to make them act as simple row markers.

The No.100 rake has its 20 teeth set at 3.8 cm spacing and the 18 teeth of No. 123 are at 3.1 cm spacing, so rows can be marked out at multiples of these distances.

If a grid pattern is required, it is a simple matter to mark further lines at right angles.

The tubes should be pushed on until they 'lock' on the bend in the tooth. They need to be firm, but please do not risk splitting the tube by using excessive force.

If any tubes should become detached in use, the white colour shows up well on the soil surface!

You may find it useful to adjust the angle of the rake teeth to make for smoother pulling through the soil.

Any questions? Get in touch and we will try to help.

Blackberry Lane (Dave & Val Taylor)

Tel: 07792 592068

Wilanson, Lapford, Crediton, Devon, EX17 6LY, U.K.

www.blackberrylane.co.uk blackberrylane.co.uk@gmail.com